



Flexo-Technic Handels GmbH

USED code 12126

*Solvent recovery Type **Renzmann M 400***



Full automatic working systems.

Vessel in mild steel.

For all alternative solvents.

Very easy to operate.

Saves money with the first start.

Keeps your plate-washer clean.



Technical information for the *Renzmann M 400*

Unit for the recovery of high boiling solvent.

- Full automatic working system.
- Electric heating
- Vacuum unit for distillation of high boiling or thermo labile solvents

Year of manufacture	1999
Volume of distillation vessel	670 litre
Constant filling volume	400 litre
Vacuum	Yes
Inline production	Possible, see schematic
Output per hour	30 - 60 litres*
Operation hours	24 hours possible
Heating up time	1 hour
Type of protection	Eexe II T 3
Operation temperature	max. 200
Vacuum abs.	max. 50 mbar
Power requirement	400 V / 50 Hz / 3Ph
Power consumption oil-heater	18 kW
Consumption cooling water	0,8 m ³ /h



* Depends on type of solvent, type and percentage of contamination

Manufactured with an ATEX Quality Assurance System Certification

Technical changes are subject to alteration.

Stand 31.10.2005 - M 400 - Code 12126